

## SilSo Lite 21025 Two-Part Liquid Silicone Foam

### Description

The product is a two-part, room temperature platinum cure, self-blowing silicone foam designed for liquid dispense. The product is ideal for potting in applications where lightweight and thermal protection are required. The viscosity profile enables excellent flow around components and is excellent for potting complex parts. The chemical composition results in a cured product that is hydrolytically stable as well as reversion resistant. The cured product provides electrical insulation and physical shock resistance of components and enables environmental protection.

### Key Features

- Low viscosity
- Fast room temperature cure
- Low smoke, flame(UL-94 V-0)\*, and toxicity upon combustion (\*UL File QMFZ2.E205830)
- Primerless chemical adhesion at room temperature to many substrates

### Key Applications

- Lightweight potting and encapsulation
- EV battery modules
- PCB staking
- Insulation

### Use and Cure Information

#### IMPORTANT:

In order to achieve optimum performance, the same lot number of the A and B components should be used. Mixed lots may not obtain the performance criteria listed on the TDS or Certificate of Analysis.

The 'A' part of the product contains the platinum catalyst; great care should be taken when using automatic dispensing equipment. Please ensure that it is not contaminated by residual hydride containing rubber (Part B) in the dispensing equipment, as curing will result. If in doubt, it is advised to thoroughly purge the equipment with a suitable hydrocarbon solvent or silicone fluid.

### Mixing

This product is designed to be dispensed by volume and mixed via static mixer. It is best practice to ensure both components are uniform by stirring, if necessary, prior to dispense and use of the product.

This silicone foam product was designed to be forgiving and process friendly. Depending on the desired flow rate of the dispense system, the static mixer used will influence foam quality. For example, dispensing through a square (8 mm by 8 mm) 32 element static mixer at 1-2 grams per second can result in high quality foam structure. Other mixer configurations may also provide good foam quality, and testing is suggested with regards to equipment-type and application. If foam cell/density quality is not to expectation, changing the dispense conditions to allow for less or greater residence time in the static mixer can influence cell structure via either dispense rate or static mixer configuration.

### Temperature

The ambient temperature of the environment, bulk silicone formulation, dispense equipment, and part in which the foam will be dispensed will influence the quality (cell structure and density) of the foam. Reaction (blowing and gelation) slow as temperature is decreased and speed-up as the temperature is increased. Ideal dispensing temperature is from 20 - 30 °C (68 - 85 °F).

### Expansion

The silicone foam product will expand by a factor of two to three times the nominal dispense volume via generation of hydrogen gas. The blowing and gelation reactions take place simultaneously upon mixing Parts A and B. When potting an enclosed container, it should be noted that the combined reactions of gelation and blowing may result in exerting pressure on the housing and components inside. The volume and rate of dispense will affect the overall density and cell structure.

### Processing and Purging

Due to the fast gel time, machine dispense is recommended. Ideally, the silicone foam is dispensed in or on the parts quickly in succession. If there is to be a gap in time between dispense stages, a purge cycle is recommended to clear the nozzle. To prevent curing in the mixer and equipment, a minimum recommended gap between dispenses or purges is approximately one-fourth of the stated gel time (i.e., if gel time is 120 seconds, a purge or dispense should take place within 30 seconds). The time and frequency in which purges are needed will be dependent on environmental conditions.

### Inhibition of Cure

Great care must be taken when handling and mixing all addition cured silicone elastomer systems, ensuring that all the mixing tools (vessels and spatulas) are clean and constructed in materials which do not interfere with the curing mechanism. The cure of the silicone can be inhibited by the presence of compounds of nitrogen, sulfur, phosphorus and arsenic; organotin catalysts and PVC stabilizers; epoxy resin catalysts and even contact with materials containing certain of these substances e.g. molding clays, sulfur vulcanized rubbers, condensation-

### Property

#### Uncured Product

Property	Test Method	Value
Color A		<b>Black</b>
Color B		<b>Translucent white</b>
Gel Time at 25°C/77°F		<b>90 seconds</b>
Mix Ratio By Volume		<b>1 to 1</b>
Mix Ratio By Weight		<b>1.17 to 1</b>
Self Bonding		<b>Yes</b>
Specific Gravity A		<b>1.17</b>
Specific Gravity B		<b>1.00</b>
Viscosity A	Brookfield	<b>20,000 cP</b>
Viscosity B	Brookfield	<b>12,000 cP</b>
Viscosity Mixed	Brookfield	<b>17,000 cP</b>

#### Cured Product

Color		<b>Opaque black</b>
Elongation at Break	ISO 37	<b>70 %</b>
Foam Density		<b>0.4 g/cc</b>
Max Working Temp		<b>200 °C / 392 °F</b>
Thermal Conductivity		<b>0.067 W/mK</b>
Thermal Conductivity (Imp)		<b>0.466 BTUin/h-ft2-°F</b>
<b>Storage</b>		
Max Storage Temperature		<b>38 °C / 100 °F</b>
Shelf Life		<b>12 mths</b>

The content set out in the technical data sheet does not contain information upon which you should rely. It is provided for general information purposes only and does not constitute a product specification. You must obtain professional or specialist advice before taking any action based on the information provided in the technical data sheet.

CHT make reasonable efforts to ensure that information set out in the technical data sheet is complete, accurate, and up-to-date. CHT do not, however, make any representations, warranties or guarantees (whether express or implied) that information set out in the technical data sheet is complete, accurate, or up-to-date or that the product will be suitable for your requirements. You should carry out your own testing to determine the applicability of such information and whether the product will be suitable. CHT reserve the right to modify the technical data sheet at any time. The CHT technical service department is available to offer further information and advice and should it be needed to look at modifying current products or custom formulate a new one to meet your specific requirements. Please contact the technical service department.

CHT Germany GmbH: Postfach 12 80, 72002 Tübingen, Bismarckstraße 102, 72072 Tübingen, Germany  
Telephone: 07071/154-0, Fax: 07071/154-290, Email: info@cht.com, Homepage: www.cht.com / www.cht-silicones.com

cure silicone rubbers, onion and garlic.

**Health & Safety**

Safety Data Sheets available on request.

Proper storage and handling are required. The Part B component can evolve hydrogen over time. It is important to avoid contact with acids and bases during storage. Product should be used in a well ventilated area during dispense.


**Packaging**

CHT silicone liquid foams are available in a variety packaging including bulk containers. Please contact our sales department for more information.

**Cure & Modulus Behavior of SilSo Lite 21025**

The below table illustrates the cure behavior of the foam at various temperatures. An example rheology curve at 25 °C is below. The start time of the experiment is approximately 1 minute after dispense.


Temperature (°C)	Temperature (°F)	Time to Modulus Crossover (min)
1.0	33.8	18.7
5.0	41.0	10.1
9.0	48.2	7.8
13.0	55.4	4.8
17.0	62.6	2.7
21.0	69.8	1.7
25.0	77.0	1.0



Revision Date 01 Jun 2023  
 Revision No 10  
 Download Date 02 Apr 2024

The content set out in the technical data sheet does not contain information upon which you should rely. It is provided for general information purposes only and does not constitute a product specification. You must obtain professional or specialist advice before taking any action based on the information provided in the technical data sheet. CHT make reasonable efforts to ensure that information set out in the technical data sheet is complete, accurate, and up-to-date. CHT do not, however, make any representations, warranties or guarantees (whether express or implied) that information set out in the technical data sheet is complete, accurate, or up-to-date or that the product will be suitable for your requirements. You should carry out your own testing to determine the applicability of such information and whether the product will be suitable. CHT reserve the right to modify the technical data sheet at any time. The CHT technical service department is available to offer further information and advice and should it be needed to look at modifying current products or custom formulate a new one to meet your specific requirements. Please contact the technical service department.  
**CHT Germany GmbH:** Postfach 12 80, 72002 Tübingen, Bismarckstraße 102, 72072 Tübingen, Germany  
 Telephone: 07071/154-0, Fax: 07071/154-290, Email: info@cht.com, Homepage: www.cht.com / www.cht-silicones.com

Modulus versus temperature profile for SilSo Lite 21025 from -90 °C to 150 °C



The content set out in the technical data sheet does not contain information upon which you should rely. It is provided for general information purposes only and does not constitute a product specification. You must obtain professional or specialist advice before taking any action based on the information provided in the technical data sheet. CHT make reasonable efforts to ensure that information set out in the technical data sheet is complete, accurate, and up-to-date. CHT do not, however, make any representations, warranties or guarantees (whether express or implied) that information set out in the technical data sheet is complete, accurate, or up-to-date or that the product will be suitable for your requirements. You should carry out your own testing to determine the applicability of such information and whether the product will be suitable. CHT reserve the right to modify the technical data sheet at any time. The CHT technical service department is available to offer further information and advice and should it be needed to look at modifying current products or custom formulate a new one to meet your specific requirements. Please contact the technical service department.  
**CHT Germany GmbH:** Postfach 12 80, 72002 Tübingen, Bismarckstraße 102, 72072 Tübingen, Germany  
 Telephone: 07071/154-0, Fax: 07071/154-290, Email: info@cht.com, Homepage: www.cht.com / www.cht-silicones.com